

Model 650 3/4" N.m/lbf.ft



The Norbar Model 650 Professional Torque Wrench is an upgrade to the Model 550 wrench and has the same high quality and accuracy as the Model 60 - 330 Professional wrenches.

Part number: 14037

EAN Bar Code: -

NATO number: -

Accuracy: +/-3%

Operates between:

130.0 - 650.0 N·m

100.0 - 480.0 lbf·ft

Model 650 3/4" square drive



TECHNICAL SPECIFICATIONS

- Length: 886 mm
- Square Size: 3/4"
- Torque Radius: 744 mm
- Weight: 4.0 Kg
- Ratchet Teeth: 60
- Ratchet Type: push-through

FEATURES

- Accuracy of +/-3% of reading.
- Non length dependent. Extension handle can be used to reduce operator effort (handle supplied as standard with Model 800, 1000 and 1500).
- Positive 'click' can be heard seen and felt.
- Long scale length in N·m and lbf·ft allows error free setting.
- Fine 60 tooth ratchet allows the wrench to be used in confined areas.