

5381906

Pipe Brush w/handle, one  
piece, 430 mm,  
Medium/hard, Yellow



Manufactured with no joint between the handle and brush head, the brush removes a common repository of dirt/food contaminants. When cleaning, it's the brush filament tips that do most of the cleaning. The brush head features extra-stiff filaments at the front, enabling you to clean more quickly and effectively.

# Technical Data

Item Number	5381906
Visible bristle length	32 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	540 Pcs
Quantity Per Layer (Pallet)	1 Pcs.
Box Length	600 mm
Box Width	295 mm
Box Height	210 mm
Product Diameter	90 mm
Length	430 mm
Width	90 mm
Height	90 mm
Gross Weight	0,2 kg
Net Weight	0,17 kg
Cubik metre	0,003 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705022001817
GTIN-14 Number (Box quantity)	15705028001825
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact