

NFC cartridge fuses, Tesys GS, cylindrical 8.5 mm x 31.5 mm, fuse type gG, 400 VAC, 8 A, without striker

Local distributor code:

388804779 DF2BN0800

EAN Code: 3389110499384

### Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	400 V AC
[In] rated current	8 A 400 V
Fuse size	8.5 x 31.5 mm
Fuse type	NFC
Quantity per set	Set of 10

## Complementary

Fuse curve	GG
Net weight	0.01 kg

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	4.8 cm
Package 1 Length	7.0 cm
Package 1 Weight	4.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	1.0 cm
Package 2 Width	4.8 cm
Package 2 Length	7.0 cm
Package 2 Weight	44.0 g
Unit Type of Package 3	S01
Number of Units in Package 3	1000
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm

Package 3 Weight 4.734 kg

# **Logistical informations**

Country of origin FR

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
PVC free	Yes

### **Use Again**

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins