

VARTA Work Flex® Motion Sensor H20 3AAA with Batt.



Water- and shock resistant Work LED Headlight with motion sensor function for hands-free working, 2 light modes (spot and flood) and a head strap with middle strap for tight fit.



Information

- Motion sensor headlight for hands-free working
- To activate the motion sensor function press on/off button for 3 seconds
- When in motion sensor mode hand wave to turn the light on or off
- High performance LED
- 8 light levels: Spot (high, low, strobe, SOS), Flood (high, low), Spot Motion Sensor, Flood Motion Sensor
- 2 light modes: spot and flood
- Shock proof 2m
- Splash-water and dust protected (IP54)
- Adjustable and washable head strap with middle strap
- Swiveling head for optimum illumination of the surroundings

Article Details

Ordernumber	18648 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	78.00 m
Runtime	20 h
Total light output	150 lm
Bulb Equipment	3 Watt LED, COB LED
Product Length / Depth mm	37.00
Product Width mm	63.00
Product Height mm	50.00
Product Weight g	72.30

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 996070	100.00	43.00	230.00	0.13
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 996087	245.00	170.00	115.00	0.62
PAL (Pallet)	756	40 08496 996094	800.00	1,200.00	1,185.00	139.16
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
9	21		189		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

