



tesa® PRO 74613

Product Information

Strong Repairing tape - best all round helper with long-lasting bonding power

Product Description

Enhance customer satisfaction with the new tesa PRO Duct Tape 74613. This duct tape offers reliable bonding power and adaptability, ensuring quick, clean, and long-lasting repairs. Whether you need to secure cables during a painting job or seal a broken pipe, our PRO Duct Tape is suitable for a wide range of surfaces.

Crafted with high materials, this duct tape is based on synthetic rubber and features a PET-fabric backing made from over 60% post-consumer recycled materials. It is the perfect addition to your craftsmen toolbox, providing easy tearability and always being ready for use.

Product Features

- Your best helper for all repairs and fixations: Quick to apply and easy to tear by hand, tesa PRO Duct Tape can be used both outdoors and indoors.
- tesa PRO Duct Tape is water repellent and works even on slightly rough surfaces. No matter the application, this tape fulfills the needs of every craftsmen.
- Backing made from more than 60% post-consumer recycled materials - increasing sustainability and reducing waste!
- Due to its design, the tesa PRO Duct Tape is easy to unwind and adapts to every product to ensure clean sealing. Making your life easier, bond by bond!
- This general purpose tape can be used for various applications such as repairing, marking, fastening, sealing and packaging.

Application Fields

This Duct Tape works best on clean, smooth surfaces. Apply the tape and press firmly onto the surface.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|---|--------------------|--------------------|------------------|
| • Backing material | PE laminated cloth | • Type of adhesive | synthetic rubber |
| • Bio-based carbon content of liner (acc. DIN EN 16640) | 63 % | • Total thickness | 175 µm |



tesa[®] PRO 74613

Product Information

Properties/Performance Values

• Elongation at break	18 %	• Hand tearability	good
• Tensile strength	41.5 N/cm	• Humidity resistance	yes
• Abrasion resistance	good	• Residue free removal	no
• Adhesive strength	Standard adhesion	• Solvent free	yes
• Ageing resistance (UV)	medium	• Tear resistance	yes
• Chemical resistance	medium		

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?mp=74613>