





Item description

Features:

- Easy mounting on 2857 Series devices
- Automatic module detection
- Capacitive user interface with slider function
- Intuitive menu navigation
- Color backlight for status indication
- Device configuration and process value visualization
- Easy copying of device configuration

Data

Geometrical Data

Width	22 mm / 0.866 Inch
Height	13 mm / 0.512 Inch
Depth	59 mm / 2.323 Inch

Mechanical data

Type of mounting	Pluggable module
------------------	------------------

Material Data

Weight	24.268 g
--------	----------

Environmental Requirements

Surrounding air (operating) temperature	-25 ... 70 °C
Surrounding air (storage) temperature	-30 ... 80 °C

Standards and specifications

Conformity marking	CE
EMC immunity to interference	EN 61000-6-2; EN 61326-2-3; EN 50121-3-2
EMC emission of interference	EN 61000-6-4; EN 61326-2-3; EN 50121-3-2



Commercial data

Country of origin	DE
GTIN	4050821677017
Customs Tariff No.	90303380900
Product Group	6 (Interface Electronics)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.