

10 ft USB 2.0 Certified A to B Cable - M/M

Product ID: USB2HAB10



The USB2HAB10 10ft USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

Features

- Supports USB 2.0 data transfer rates up to 480 Mbps
- USB-IF Certified Hi-Speed USB 2.0 (480 Mbps)

	Warranty	Lifetime
Hardware	Connector Plating	Nickel
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB B (4 pin) Male
Physical Characteristics	Cable Length	3 m [10 ft]
	Color	Black
	Product Length	3 m [10 ft]
	Weight of Product	133.3 g [4.7 oz]
	Wire Gauge	22/28 AWG
Packaging Information	Package Height	20 mm [0.8 in]
	Package Length	22 cm [8.7 in]
	Package Width	12 cm [4.7 in]
	Shipping (Package) Weight	134.3 g [4.7 oz]
What's in the Box	Included in Package	1 - 10 ft USB 2.0 Certified A to B Cable - M/M

Product appearance and specifications are subject to change without notice.