

DELTA 3

ID: Silver & Grey

UPS: <10 ms

Battery Pack Waterproof Level: IP65

Volume: 600W <30 dB/1200W <40 dB

Warranty: 5 Years



General

Capacity

1024Wh

Dimensions

398x200x284 mm, 22.549 L

DELTA 3 Extra Battery Dimensions

1kWh capacity

398x200x198 mm 15.8 L

Net Weight

≤12.5 kg

App

Supported (TOU/Storm warning)

Extra Battery

Expandable capacity to 5kWh

D2M/D2/DP3/D3 EB Supported

Output

Total Output Ports

11

Max Device(s) Power Supported by X-Boost

2400W

USB-A × 2

/

Car Power × 1

12.6V, 10A, 126W Max

AC × 4

4 × 1800W (Surge 3600W)

USB-A × 2 (Fast charging)

2 × 18W Max

USB-C × 2

2 × 100W Max

DC5521 × 2

2 × 12.6V, 3A Max

Input

AC charging

1500W (56 Min)

Smart Generator charging

1500W (56 Min)

AC+PV charging

1500W (56 Min)

Solar charging

DC input 11V-60V

1 × 500W Max (130 Min)

Car charging

800W (1.3 Hr with Alternator Charger)

Battery

Chemistry

LFP

Cycle Life

4000 Cycles to 80% Capacity