



verso mobile storage bench with 1 drawer-door cabinet / 1 drawer-door cabinet. Featuring a robust, steel channel framework with integrated storage units 125mm diameter castors and a 30mm multiplex wood worktop. Delivered assembled. Equivalent cabinet - WxDxH:525/525x550x600mm. Drawer configuration: 2x 125mm with 100% extension slides (75kg U.D.L.) with two, reinforced 350 mm doors. Finished in durable powder coat paint in RAL 7035 light grey / RAL 5010 gentian blue. WxDxH: 1250x600x830mm.

Breite [mm]: 1250
Tiefe [mm]: 600
Höhe [mm]: 830
Bruttogewicht [kg]: 88.89
EAN-Code: 5039350028506
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Gentian blue
Main RAL colour	RAL 5010
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	2
Drawer load capacity [kg]	75
Drawer height 1 [mm]	125
Drawer height 2 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Beech Multiplex
Door type	Plain
Door height 1 [mm]	350