

Specialist heavy-duty vacuum cleaner, perfect for use in bakeries

## Equipment:

- Flat pleated filter PES
- Auto shutdown when max. level is reached
- Antistatic system
- Container material Plastic
- Eco filter system
- Heat-resistant plastic container
- Filter cleaning Tact Filter Clean
- Safety class I
- Caster with brake
- Maintenance -free suction fans 1 piece(s)

Order no.: 1.184-700.0



## Technical data

Air flow rate (l/s)	57
Vacuum (mbar/kPa)	235/23.5
Container capacity (l)	35
Max. intake performance (W)	1380
Performance disposal pump (A)	-
Standard nominal size (mm)	35
Length of cord access. (m)	7.5
Sound level (db(A))	63
Weight (kg)	12.8
Dimensions (L x W x H) (mm)	505x370x540

## Details

### Description

The NT 35/1 Tact Bs is a user-friendly vacuum cleaner designed specifically for the bakery and confectionery industry. With a container volume of 35 litres, this machine is a one-motor wet/dry vacuum cleaner featuring TACT - an innovative, patented, auto filter clean system. The special PES flat pleated filter system allows changing between wet and dry vacuuming without filter change. The NT 35/1 Tact Bs is equipped with an antistatic system up to the suction hose connection, accessory holder for the storage of baking oven nozzle or the baker's kit (both special accessories) with heat resistant container and rubber power cable. Please note that this machine is supplied without hose, suction tubes or tools - two accessory kits are available to suit your application.

---

### Features & Benefits

The vacuum cleaner for bakeries

The optional accessory kits were developed specially for use in bakeries.

The plastic container is acid, lye and heat resistant.

Heat-resistant PES flat pleated filter

The machine has a heat-resistant PES flat pleated filter, dust class M – ideal for effortless removal of dust and dirt in bakeries.

---

## Accessories

### Adapter (tube -> nozzle)

#### Adapter ID 35 - 40 (tube -> nozzle)

From DN 35 to DN 40: Plastic adapter (electrically non-conductive). Suitable for NT vacuum cleaners.

Order no. 6.902-084.0



### All-purpose brushes

#### All-purpose brush

Natural bristles (ox hair), bristle element 120 x 45 mm.

Order no. 6.903-863.0



### All-purpose nozzles (wet/dry)

#### Wet and dry floor tool

All-purpose plastic nozzle (DN 35) with 300 mm working width. With side rollers, brush strips (6.903-278.0) and squeegees (6.903-277.0). Only for NT vacuum cleaners.

Order no. 6.906-512.0



#### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.903-018.0



#### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle (DN 40) with 450 mm working width. With height-adjustable side rollers, brush strips (6.903-065.0) and oil-resistant squeegees (6.906-146.0). Only for NT vacuum cleaners.

Order no. 6.906-383.0



#### All-purpose nozzle (wet and dry), DN 35

All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.

Order no. 6.906-384.0



#### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 35) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.

Order no. 6.906-513.0



## All-purpose nozzles (wet/dry)

### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 40) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.

Order no. 6.906-554.0



## Baking oven nozzle

### Baking oven nozzle, ID 35, 350mm

Aluminium, for cleaning baking ovens with rubber lip 6.900-517.0 and supporting lip 6.900-518.0, je 2 x.

Order no. 4.130-104.0



### Baking oven nozzle, ID 35

For cleaning baking ovens with scratch bar.

Order no. 4.130-173.0



## Bend metal

### Bend, DN 35, metal

Robust, chromium-plated metal bend (DN 35), can be used instead of a plastic bend (with clip system adapter 5.407-112.0; C 35-DN 35, plastic, el.).

Order no. 6.900-519.0



### Bend, DN 40, metal

Robust, chromium-plated metal bend (DN 40), can be used instead of a plastic bend (with clip system adapter 5.407-111.0; C 40-DN 40, plastic, el.).

Order no. 6.900-276.0



## Bend stainless

### Bend, stainless steel ID 35

Stainless steel and crooked, ID 35

Order no. 6.903-141.0



### Bend, stainless steel ID 40

Stainless steel and crooked, ID 40

Order no. 6.902-079.0



## Car cleaning nozzles

### Car vacuuming tool DN 35

Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.

Order no. 6.906-108.0



## Combi-nozzles (dry)

### Combination floor tool (dry)

Combination floor tool with changeover function, plastic (272 mm). With stainless steel base plate, thread catcher 6.905-417.0 and DN 35 connection.



Order no. 6.906-511.0

## Connecting sleeve C-DN (clip on taper), EL (electroconductive)

### C-ID 35 adapter

Connects C 35 hose for ID 35, electrically conductive.



Order no. 5.407-112.0

### C 40 adapter

Electrically conductive adapter (C 40) with DN 35 connection for connecting DN 35 accessories to an industrial C 40 or C-DN 40 suction hose. Suitable for NT vacuum cleaners.



Order no. 5.407-109.0

## Crevice nozzles

### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 210 mm.

Order no. 6.900-385.0



### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 370 mm.

Order no. 6.900-922.0



### Crevice tool

Plastic crevice tool (DN 40) for vacuuming in crevices and corners. Length: 290 mm.

Order no. 6.903-033.0



### Crevice tool

Metal crevice tool (DN 40) for vacuuming in crevices and corners. Length: 400 mm.

Order no. 6.905-817.0



### Crevice tool ID 35.

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 250 mm.

Order no. 6.906-240.0



## Crevice tools

### Grout nozzle, synthetic

Grout nozzle, plastic, 370 mm

Order no. 6.900-222.0



## Crevice tools

### Grout nozzle, stainless steel

Grout nozzle, stainless steel, 400 mm

Order no. 6.900-926.0



## Extension hoses (Clip-system)

### Extension hose, C 32, C 35 clip system

Electrically non-conductive standard extension hose for all C-32 and C-35 hoses with clip system.

Order no. 6.906-237.0



### Extension hose, C 40

2.5 m electrically non-conductive standard extension hose for all C-40 hoses with clip system.

Order no. 6.906-344.0



### Extension hose C 32-, C 35-Clip-system, el.

for all C-32 and C-35 hoses, electrically conductive.

Order no. 6.906-277.0



## Flat pleated filter (PES)

### Flat pleated filter (PES)

Flat pleated filter (PES) – BIA-C dust class M: rotproof polyester fleece, ideal for wet use and abrasives. Standard for NT 35/1 Eco BS and NT 55/1 Eco BS.

Order no. 6.904-360.0



## Fleece filter bags (3 ply)

### Fleece filter bags, x 5

3-ply tear-resistant fleece filter bags (dust class M). For dry pick up, suitable for the following models: NT 361 Eco, Eco TE, TE-A and NT 361 Eco M, NT 35/1 Eco, Eco Te, Eco M. Contents: x5

Order no. 6.904-351.0



## Membrane filter / fabric filter

### Membrane filter/fabric filter

Polyester needle fleece membrane/fabric filter, washable up to 40°C, suitable for all NT 361 Eco to NT 611 Eco versions as an alternative to a filter bag.

Order no. 6.904-212.0



## Miscellaneous

### Extension cable

Extension cable, 20 m, 3x1.5 mm². With splash-proof earthing pin plug, strain relief and anti-kink sleeve.

Order no. 6.647-022.0



## Nozzle sets

### Nozzle kit

Nozzle kit for all NT vacuum cleaners with DN 35 accessories includes crevice tool, upholstery tool, round brush (x3)

Order no. 2.860-116.0



## Other nozzles

### Aluminium surface nozzle

Flat surface nozzle cpl. DN 51, 200 mm, aluminium with brush and stainless steel bumper

Order no. 4.130-415.0



## Paper filter (2 ply)

### Paper filter bags, x 5

5 paper filter bags. BIA-(U, S, G, C) dust class M. For all NT 361 Eco models (except Eco H).

Order no. 6.904-210.0



## Pipe dusting nozzles

### Pipe dusting nozzle, ID 35

Plastic, pipe diameter 100 mm

Order no. 6.903-035.0



### Pipe dusting nozzle

Plastic, pipe diameter 200 mm

Order no. 6.903-036.0



## Plastic bend

### Plastic bend

Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).

Order no. 5.031-718.0



### Plastic bend

Electrically conductive plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models.

Order no. 5.031-939.0



### Plastic bend, ID 35

Plastic, ID 35.

Order no. 6.902-009.0



## Radiator brushes

### Radiator brush

Radiator brush is suitable for crevice tool 6.900-385.0 or 6.905-240.0.

Order no. 6.903-034.0



## Reducer (tube -> nozzle)

### Reducer

Reducer for accessory extension. Ideal for accessories with DN 35 connecting cone in combination with accessories with DN 40 connecting cone.

Order no. 6.902-017.0



### Reducer from ID 35 to 32

Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.

Order no. 6.902-072.0



## Reducing sleeves

### Reducer

Threaded reducer - from C-40 to DN 35. Suitable for NT vacuum cleaners.

Order no. 5.407-108.0



## Repair kits

### Repair set, C 35

Repair set (C35) includes threaded hose adapters (without bayonet adapter) for industrial NT vacuum cleaners with clip system.

Order no. 2.639-682.0



## Rubber suction tools, nose 45°

### Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 35), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

Order no. 6.902-104.0



## Set reducing / extension sleeves

### Set reducing / extension sleeves

ID 40/35, ID 35/32 (tube -> nozzle), plastic.

Order no. 2.860-117.0



## Special filter bags, wet filter bags

### Special filter bag, wet filter bag

Approved for dust class L, general cleaning, wet and dry, tear-resistant.

Order no. 6.904-171.0



## Special hoses

### Special suction hose, ID 35, heat-resistant

For cleaning baking ovens, temperature resistant up to 350 °C

Order no. 4.440-731.0



## Suction brushes

### Suction brush

Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.

Order no. 6.903-862.0



## Suction hoses (Clip-system)

### Suction hose

4 m suction hose without bend and adapter. With bayonet at vacuum end and C 35 clip connection at accessory end.





## Suction hoses (Clip-system)

Order no. 6.906-241.0

### Suction hose

2.5 m electrically conductive suction hose without bend and adapter with bayonet at vacuum end and C 35 clip connection at accessory end.



Order no. 6.906-275.0

### Suction hose (clip system), C 35, el.

4 m electrically conductive suction hose without bend and adapter with bayonet at vacuum end and C 35 clip connection at accessory end.



Order no. 6.906-500.0

### Suction hose

4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.



Order no. 6.906-321.0

### Suction hose

Electrically conductive, 4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.



Order no. 6.906-546.0

### Suction hose (clip system), C 40, 10 m, el.

Suction hose with bayonet coupling, electrically conductive.



Order no. 6.906-877.0

### Suction hose (clip system), C 35

Electrically conductive, 10 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.



Order no. 6.906-242.0

## Suction hoses complete

### Suction hose, complete

Standard, 4.0m, ID 35

Order no. 4.440-287.0



### Suction hose complete, ID 35, 2,5m

Temperature-resistant to 120 °C.

Order no. 4.440-339.0



## Suction hoses complete (Clip-system)

### Suction hose

2.5 m standard suction hose with bend, bayonet at vacuum end and C 35 clip connection at accessory end. Without PDFC module. Standard for NT 27/1/Me Advance und NT 48/1.



Order no. 4.440-626.0

### Suction hose

2.5 m electrically conductive suction hose with bend, bayonet at vacuum end and C 35 clip connection at accessory end. Without module.



Order no. 4.440-653.0

## Suction tubes metal

### Suction tube

Chromium-plated metal suction tube (DN 35, 1x0.5 m), standard for virtually all single-motor industrial NT vacuum cleaners.

**Order no. 6.900-514.0**



### Suction tube

Chromium-plated metal suction tube (DN 40, 1x0.5 m), standard for virtually all two-motor industrial vacuum cleaners. Optional for industrial single-motor NT vacuum cleaners with DN 40 suction hose.

**Order no. 6.900-275.0**



## Suction tubes plastic

### Suction tube, DN 35

Plastic suction tube (DN 35, 1x0.5 m) only suitable for BV and T vacuum cleaners.

**Order no. 6.900-384.0**



## Suction tubes stainless steel

### Suction tube, ID 40

Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.

**Order no. 6.902-081.0**



### Suction tube

Stainless steel suction tube (DN 40, 1.0 m) only suitable for NT vacuum cleaners.

**Order no. 6.906-531.0**



## Target group specific vacuum cleaner accessory sets

### Oven kit

Accessory kit for vacuuming and cleaning ovens in bakeries, cake shops, etc.

**Order no. 2.640-341.0**



### Bakery kit

Accessory kit for vacuuming and cleaning bakeries, equipment, shelves, etc. Ideal for bakeries, cake shops, etc.

**Order no. 2.640-436.0**

