

Metal tool box with assortment, 146 pieces 1/2 ", metric, 1483KHD3RB-FF4



Article number: 1483KHD3RB-FF4

Size: 523x257x300cm

Weight: 11,000 g

Packing quantity: 1pc. "

146-piece Metal tool case, range 1/2 "

Lid Compartment – 4 pieces



481-400 Hammer	400g
3625N-35 Superflex plastic hammer	415g
2509 Flexible gripper	525 mm
2535F2 Magnetic lifter	1kg

Foam insert socket 1/2", 49-piece



Inserts 1/2 ", short	7800SM	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27, 30, 32
1/2 "screwdriver bits for hexagon socket screws	7809M	5, 6, 7, 8, 10, 12, 14, 17, 19
1/2 "screwdriver bits for TORX® screws	7809TORX	T20, T25, T27, T30, T40, T45, T50, T55, T60
T-handle 1/2 "	8154-1 / 2	-
Ratchet 1/2 ", narrow head	8150SL	-
Extension 1/2 "	8160-1 / 2	125 mm
Extension 1/2 "	8162-1 / 2	250 mm
3/8 "to 1/2" transitional part	8164-1 / 2	-
Universal joint 1/2 "	8166-1 / 2	-
1/2 " to 3/8" transitional part	8165-1 / 2	-
1/2 " 3/4 " transitional part	8964	-
Bit holder 1/2 "	7807H	-
Combination spanner	111M	24, 27, 30, 32
Open-ended spanner	6M	24x27, 30x32

Foam insert Screwdriver, 53-piece



Screwdriver with pistol grip	808050P	-
Screwdriver, short version	808050S	-
Bit-Box, 31-piece set	59 / S31-1	-
Double angled offset screwdriver for slotted screws	2047-0.8-4	0,8x4x100
Double angled offset screwdriver for Phillips screws	2047PR-1-2	PH1, 2
Ergo screwdriver for slotted screws	BE-8020L	0,5x3x75
Ergo screwdriver for slotted screws	BE-8030	0,6x3,5x75
Ergo screwdriver for slotted screws	BE-8155	1,2x6,5x125
Ergo screwdriver for slotted screws, hex shaft and approach	BE-8260	1,6x8,0x175
Ergo Screwdriver for slotted screws, short version	BE-8350	1x5,5x25
Ergo screwdriver for Phillip screws, short version	BE-8601/ BE 8602	PH1x25, PH2x25
Ergo screwdriver for Phillip screws	BE-8610/ BE 8620	PH1x75, PH2x100Angle
screwdriver set, with ball, 9-piece	BE-9770	HEX 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10

12-piece



Tape measure	MTB-3-16-E	3m
Ergo side cutter	2101GC	160mm
Ergo nose pliers, bent, chromed	2427 GC-200 IP	200mm
Ergo nose pliers, long, chrome-plated	2430 GC-200 IP	200mm
Ergo combination pliers, chrome-plated	2628 GC-160IP	160mm
Ergo Water Pump Pliers	8224CIP	-
Driver	3734	Ø 3, 5, 8mm
Grains	3735-4-120	120mm
Scriber cranked,	1177-SCRIBE	230mm
Calipers	1150-1 / 2 H / P	150mm

28-piece



Combination spanner	BE-111M	6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22
Open-ended spanner	BE-6M	6x7, 8x9, 10x11, 12x13, 14x15, 16x17, 18x19, 20x22
Ergo Adjustable Wrench 6 ", chromed	9070C	158x20 mm
Telescopic articulated mirror	5515T-52	Ø 50 mm
Electricians knife with plastic handle	2820EF2	-
LED Flashlight	BFLA01	-