

SAKAP 2.5-4



General ordering data

Version	End and partition plate for terminals, grey, Height: 39 mm, Width: 1.5 mm, V-O, PA 66/6
Order No.	1129460000
Type	SAKAP 2.5-4
GTIN (EAN)	4032248970643
Qty.	20 items

SAKAP 2.5-4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	33.15	Depth (inches)	1.3051 inch
Height	39 mm	Height (inches)	1.5354 inch
Width	1.5 mm	Width (inches)	0.0591 inch
Net weight	2.05 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66/6	Colour	grey
UL 94 flammability rating	V-0		

System specifications

Version	End and intermediate plate	PE connection	No
---------	----------------------------	---------------	----

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		