



**Part Number :** [349861602](#)

**Product Description :** MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 16 Circuits, Keying Option B, without Connector Position Assurance, Light Gray

**Series Number :** 34986

**Status :** Active

**Product Category :** Connector Housings



---

## Documents & Resources

### Drawings

[349861602 sd.pdf](#)

[PK-31300-514-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-33472-100-001.pdf](#)

[AS-33472-100-CH-001.pdf](#)

[AS-33472-100-FR-001.pdf](#)

[PS-33476-000-001.pdf](#)

[334760000-PS-CH-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Dodecamethylcyclohexasiloxane;

	Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	34986
Description	MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 16 Circuits, Keying Option B, without Connector Position Assurance, Light Gray
Application	Power, Wire-to-Wire, Automotive
Comments	Without Connector Position Assurance (CPA), See Product Specification for maximum current rating by wire AWG
Product Name	MX150
UPC	887191418032

### Physical

Circuits (maximum)	16
Color - Resin	Gray (Light), Natural
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	23.655/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

#### Mates With / Use With

##### Mates with Part(s)

Description	Part Number
MX150 Hybrid Mat-Sealed Female Connector Assemblies	<u>34985</u>

##### Use with Part(s)

Description	Part Number
MX150 Male Terminals	<u>31296</u>
MX150 Male Terminals	<u>33000</u>