

221626000

Polyester enclosure Mini-Polyglas 160 x 260 x 100 mm

Polyester enclosure Mini-Polyglas 160 x 260 x 100 mm

Catalogues | Declaration of Conformity | Drawing | 3D Data

Technical data

Height	160 mm
Width	260 mm
Depth	100 mm
Material	Polyester
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-30 °C
temperature max.	90 °C
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10^12 Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tarif number	39269097
Weight	1.6 kg
GTIN	4250157915658


ETIM classification

ETIM 8	EC000261

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100112080
Mounting plate for 21.162600

Zubehör - s. Zeichnung
Accessories - see drawing

216300030
Triangular locking screw (8 mm)

Zubehör - s. Zeichnung
Accessories - see drawing

216300040
Square locking screw (8 mm)

Zubehör - s. Zeichnung
Accessories - see drawing

216300050
Phillips locking screw

Zubehör - s. Zeichnung
Accessories - see drawing

216300240
Square locking screw (6 mm)