



Main

Range of product	Rilux
Product or component type	Emergency light fitting
Function	Standard
Supply	Non-maintained
Light source	LED 0.3 W x 12
Number of batteries	1 x 6 V 4 Ah

Complementary

[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	36.8 VA
Electrical insulation class	Class II
Autonomy	4 h
Charging time	24 H
Luminous flux	300 Lm
Device mounting	Surface ceiling Surface wall
Height	620 Mm
Width	120 Mm
Depth	56 Mm
Net weight	1.6 Kg

Environment

IP degree of protection	IP40
IK degree of protection	IK06
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Standards	EN 60598-2-22 EN 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.6 Kg
Package 1 Height	62 Cm
Package 1 width	12 Cm
Package 1 Length	5.6 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**