

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/in/products/1409283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marshalling panel, design: 19" rack/fixed housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection, housing size: 1, color: light grey RAL 7035



Product description

Marshalling distributor panel, 19", 1 RU, with 5 metal brackets

Your advantages

- Robust design
- For easy cable management

Commercial data

Item number	1409283
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABN
Product key	ABNLBZ
Catalog page	Page 50 (NTK-2014)
GTIN	4046356867078
Weight per piece (including packing)	822.9 g
Weight per piece (excluding packing)	822.9 g
Customs tariff number	94039910
Country of origin	CN

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/in/products/1409283>

Technical data

Product properties

Product type	Data plug
Type	1RU

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Width	482.6 mm
Height	44.45 mm
Drill hole distance, horizontal	31.6 mm

Material specifications

Color	light grey RAL 7035
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	Steel, powder-coated
Housing surface material	Powder-coated, gray

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

Mounting

Mounting type	19" rack
---------------	----------

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/in/products/1409283>

Classifications

ECLASS

ECLASS-11.0	27440210
ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/in/products/1409283>

Accessories

CUC-PP-FRAME-19 - 19" mounting frame

1407986

<https://www.phoenixcontact.com/in/products/1407986>

19" panel mounting frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 7035



CUC-PP-FRAME-19 BK - 19" mounting frame

1409140

<https://www.phoenixcontact.com/in/products/1409140>

19" frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 9005



CUC-PP-PATCHBAY-MH - Marshalling panel

1409283

<https://www.phoenixcontact.com/in/products/1409283>



CUC-PP-FRAME-19 - 19" mounting frame

1407986

<https://www.phoenixcontact.com/in/products/1407986>

19" panel mounting frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 7035



FOC-SB-FRAME-19-LC:12-OM2 GY - Splice box

1418815

<https://www.phoenixcontact.com/in/products/1418815>

Splice box, design: 19" rack patch module, degree of protection: IP20, material: Sheet steel, connection method: Splicing, housing size: 1, color: light grey RAL 7035, Ethernet



CUC-PP-PATCHBAY-MH - Marshalling panel

1409283

<https://www.phoenixcontact.com/in/products/1409283>



FOC-SB-FRAME-19-LC:24-OM2 GY - Splice box

1418816

<https://www.phoenixcontact.com/in/products/1418816>

Splice box, design: 19" rack patch module, degree of protection: IP20, material: Sheet steel, connection method: Splicing, color: light grey RAL 7035, Ethernet



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in