



tesa® 55810

Universal Double Sided Tape with Nano Power

Product Information

tesa® Universal Tape – Nano Power Adhesive Tape – Double-Sided, Transparent and Reusable – Easily Removable Mounting Tape for Indoor and Outdoor Use – Holds up to 5 kg per Metre

Product Description

The tesa® Universal Nanotape can be stored in any drawer or toolbox and is easily on hand whether on the road, in a car or camper van. The double-sided tape offers great adhesive strength and can withstand high loads, also over time. It can be removed completely residue-free from smooth and firm surfaces, washed and then reused. The practical dispenser also enables simple and time-saving unrolling.

Product Features

- Versatile: The nanotape is ideal for mounting, decorating and organising, both indoors and outdoors
- Inconspicuous hold: Fix objects discreetly thanks to the almost invisible, transparent tape
- All-rounder: For use on all firm, smooth surfaces – not suitable for wallpaper and plaster
- Reusable: The tape can simply be removed and then reapplied
- Strong alternative to nails and magnets: The adhesive tape is strong and durable – it can hold up to 5 kg/m
- Handy: The dispenser makes the tape easy to unroll, apply and store
- Non-damaging: The nanotape can be easily removed from smooth surfaces without leaving any residue
- Scope of delivery: 1 x roll of tesa® Universal Nano Power Double-sided Mounting Tape

Application Fields

- Versatile: The nanotape is ideal for mounting, decorating and organising, both indoors and outdoors
- Inconspicuous hold: Fix objects discreetly thanks to the almost invisible, transparent tape
- All-rounder: For use on all firm, smooth surfaces – not suitable for wallpaper and plaster
- Reusable: The tape can simply be removed and then reapplied
- Strong alternative to nails and magnets: The adhesive tape is strong and durable – it can hold up to 5 kg/m
- Handy: The dispenser makes the tape easy to unroll, apply and store
- Non-damaging: The nanotape can be easily removed from smooth surfaces without leaving any residue
- Scope of delivery: 1 x roll of tesa® Universal Nano Power Double-sided Mounting Tape

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|---------|-------------------------------|--------|
| • Type of adhesive | acrylic | • Holding power of tape up to | 5 KG/M |
| • Total thickness | 2000 µm | | |



tesa[®] 55810

Universal Double Sided Tape with Nano Power

Product Information

Properties/Performance Values

• Ageing resistance (UV)	yes	• Humidity resistance	yes
• Application temperature from	-20 °C	• Residue free removal	yes
• Application temperature to	120 °C	• Suitable surfaces	Tiles, Most plastics, Glass, Metal, Steel
• Applicationfield	Office, Garden, Garage, Bathroom, Living room, Bedroom, Children's room, Hall, Home		

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?mp=55810>