

Protective covers - VS-08-SD-F-BK - 1658066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Protective cover, IP67, flat design, to cover the contact insert in the panel mounting frame, color: black



Ethernet

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	3.46 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Mechanical characteristics

Connection profile	RJ45
Locking type	without
Color	black

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Degree of protection	IP67

Material data

Flammability rating according to UL 94	V0
Housing material	PA
Material	Plastic
Sealing material	EDPM, self-greasing
Seal material	EDPM, self-greasing

Standards and Regulations

Protective covers - VS-08-SD-F-BK - 1658066

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27149110
eCl@ss 5.1	27149110
eCl@ss 6.0	27261210
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002314
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Protective covers - VS-08-SD-F-BK - 1658066


Approvals

Approval details

EAC

Drawings

Dimensional drawing



Protective cover, IP67
