

Trend Spot

TREND SPOT LED MONO WH 36° 830

0053384



Range features

- Integrated LED luminaire with LED driver
- 540 lumen output / 10W
- Beam Angle 30° / 3000K Warm White
- High quality aluminium construction
- Multi-directional 25° tilt
- High Powered Single LED – 10W
- Size 97x97mm. Cutout: 90mm
- Halogen optical effect
- Extra long life – 50,000hrs
- Available in white and brushed aluminium

LED

PRODUCT OVERVIEW

Ordering number	0053384
Light colour	Warm white
Technology	LED
Average life (Rated) (h)	50000
EAN code	5410288533858
Certifications	ENEC
Mount	Ceiling recessed
Housing	Steel
CRI (Ra)	90
LOR (%)	100
Beam angle(°)	30
Efficacy (Rated) (lm/w)	54
Voltage (V)	220-240
Colour	White
IP rating	20
IK rating	02

Trend Spot

TREND SPOT LED MONO WH 36° 830

0053384

DATA TABLE

General data

Technology	LED
Ordering number	0053384
Average life (Rated) (h)	50000
EAN code	5410288533858
Certifications	ENEC
Mount	Ceiling recessed
Long description	Integrated LED luminaire with LED driver. 540 lumen output / 10W. Beam Angle 30° / 3000K Warm White. High quality aluminium construction. Multi-directional 25° tilt . High Powered Single LED – 10W. Size 97x97mm. Cutout: 90mm. Halogen optical effect . Extra long life – 50,000hrs. Available in white and brushed aluminium
Product name	TREND SPOT LED MONO WH 36° 830
Control gear type	External
Environment	Interior
General application	Residential accent down lighting
Housing	Steel

Optical data

Light colour	Warm white
CRI (Ra)	90
LOR (%)	100
Beam angle(°)	30
Luminous flux (Nominal) (lm)	540
Distribution type	Direct

Electrical data

Efficacy (Rated) (lm/w)	54
Voltage (V)	220-240
Drive current (mA)	800mA
Electrical protection	CLASS II

Trend Spot

TREND SPOT LED MONO WH 36° 830

0053384

Physical data

Weight (kg)	0.5
Colour	White
Lamp included	Yes
Height (mm)	50
Width (mm)	97
Length (mm)	97
IP rating	20
IK rating	02
Vertical tilt (°)	25
Horizontal rotation (°)	25
Cutout diameter (mm)	85 ø
Cutout shape	Square
Recessed depth (mm)	50
Diffuser finish	Unique LED optic - creates halogen feel and look

Trend Spot

TREND SPOT LED MONO WH 36° 830

0053384

TECHNICAL DRAWINGS



ENERGY LABEL

