

Sheetsteel housing **BGUK 10**



Advantages

- Integrated Rail System for the installation of different product sizes
- Excellent corrosion protection and high abrasion resistance through powder-coated surface RAL 5008
- With cooling fins for optimal heat extraction
- Faceplate without cooling fins for individual connection options
- Integrated crane eyes
- Optionally available in degree of protection IP 54

Approvals



Sheetsteel housing BGUK 10

Type		BGUK 10
Electrical data	Operating data	
	For power (single phase)	1600 VA
	For power (three phase)	750 VA
	Max. Power loss (at 40 °C ambient temperature)	110 W
	Enclosure suitable for protection index	IP 23
Order numbers		
Order Number		BGUK 10

Type		BGUK 10
Mechanical data	Terminal and mounting	
	Floor mounting	Yes
	Wall mounting	Yes
	Cable glanding type	M25
	Cable glanding Ø	9 - 14 mm
	Measures and weights	
	Weight	7.00 kg
	Dimension (W x H x D)	320 x 265 x 200
	Effective inside dimension (W)	235 mm
	Effective inside dimension (D)	155 mm
Effective inside dimension (H)	220 mm	
Fixing hole Ø	9 mm	
Accessory		
Front plate (optional)	BGUKF 10	