

LED RECHARGEABLE ULTRA-SLIM WORKLIGHT

Product Specifications

SPECIFICATIONS	OBS-WL4
Color	Grey/Red
Material	Aluminum/Plastic
Luminosity (Lumen)	700 (Turbo Mode) 500 (Front Flood Light - High Mode) 150 (Front Flood Light - Low Mode) 80 (Top Light)
Rechargeable	Yes
Battery Type	Lithium-Ion
Runtime	30s (Turbo Mode) 1h (Front Flood Light - High Mode) 3.5h (Front Flood Light - Low Mode) 4.5h (Top Spot Light)
Charge Time	2.5h
Charging Port	USB-C
Weight	1.5 oz / 42.5 g
Length	4.2 in / 106 mm
Width	1.0 in / 26 mm
Height	0.6 in / 14 mm
Storage/Operating Temperature	+15°F to +120°F / -10°C to +50°C
IP Rating	IP54
IK Rating	IK07
Ultra-Slim Design	Yes
Dimming	Yes
Magnet	Yes
Accessories	Charging Cable