



PRODUCT-DETAILS**BVNV-P488****CONDFTNG STR PG48 NW48 IP68 CSA BLK**

General Information

Extended Product Type:	BVNV-P488
Product ID:	7TAA292150R0316
EAN:	7630030230912
Catalog Description:	CONDFTNG STR PG48 NW48 IP68 CSA BLK
Long Description:	VN Straight Connector, PG Thread for IP68 Static Conduit - Thread PG 48, Fits to Conduit Size NW/Metric 48/50, Color Black
Display Name:	BVNV-P488

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	Use In Railway Vehicle and Heavy Machine Construction
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030230912
UPC:	786209952721

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide 6
Size:	NW48 , PG48 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	30 EA
Package Level 1 EAN:	7630030230912
Package Level 1 Height:	200 mm 7.874 in
Package Level 1 Depth / Length:	399.999 mm 15.748 in
Package Level 1 Width:	299.999 mm 11.811 in

Certificates and Declarations

Data Sheet, Technical Information:	BVNV-P488
Instructions and Manuals:	BVNV-P488
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

