



Cordless MULTIMASTER AMM 500 Plus Top

Battery-powered oscillating multi-tool

The powerful cordless MultiTool for rapid work progress (in interior work and renovation) with more than 30 accessories – for sawing in wood and metal, sanding, removing tiles and much more.

Product number: 7 129 33 61 00 0

Details

- > Anti-vibration system: continuously safe and pleasant working thanks to minimal vibrations and outstanding noise insulation.
- > StarlockPlus tool mounting: more work progress and greater precision thanks to 100% power transmission without losses.
- > QuickIN: tool changes in less than 3 seconds thanks to the patented tool-free FEIN rapid clamping system.
- > With the StarlockPlus tool mounting, you can access around 100 FEIN accessories from the Starlock and StarlockPlus performance classes.
- > DC motor: effective and powerful motor technology offering virtually the same power as the mains-powered version.
- > Tacho generator: constant speeds even under load and infinitely variable electronic speed control.
- > Metal gearbox: ability to withstand high loading and outstanding service life because all the gearbox parts are made from metal.
- > Mechanical interface: for stationary operation in the table or drill jig holder or for securing the depth stop.
- > SafetyCell technology: perfect protection against overload, overheating and total discharge thanks to Li-ion batteries with individual cell monitoring.
- > The battery charge can be read off the battery.

Price includes

- ✓ 1 E-Cut long-life saw blade (10 mm)
- ✓ 2 E-Cut long-life saw blades (65 mm)
- ✓ 1 carbide saw blade (diameter 75 mm)
- ✓ 1 Stopper knife
- ✓ with 5 sanding sheets, with holes for each of grit sizes 60, 80, 120, 180
- ✓ 1 rapid charger ALG 80
- ✓ 1 plastic carrying case
- ✓ 2 E-Cut long-life saw blades (35 mm)
- ✓ 1 E-Cut carbide Pro saw blade (32 mm)
- ✓ 1 HM rasp (triangular)
- ✓ 1 Sanding plate with holes
- ✓ 1 dust extraction device
- ✓ 2 Li-ion battery packs (18 V / 3 Ah)

Product feature

- ✓ Mechanical interface



Technical data

TECHNICAL DATA

Battery voltage	18 V
Battery capacity	3 Ah
Battery compatibility	Li-ion / HighPower Li-ion
Battery interface	18 V
Oscillations	11,000 - 18,500 rpm
Tool Holder	StarlockPlus
Tool change	QuickIN
Amplitude	2 x 1,7°
Weight with battery	1.80 kg
Weight without storage battery	1.30 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA
Uncertainty of measured value
KpA

74 dB
3 dB

Sound power level LWA
Uncertainty of measured value
KWA

85 dB
3 dB

Sound peak value

87 dB

LpCpeak
Uncertainty of measured value
KpCpeak

3 dB

Application examples

