

6227-0006 Light Duty Single Footswitch



- Low profile, rear hinged switch designed for improved user comfort
- All plastic construction with raised tread pattern and anti slip pad
- Black cover with black base
- Supplied with 2 meters of black 2 core cable free wire ends
- Single pole normally open contacts
- Momentary action
- Sealed to IPX2
- Electrical rating: 6A 250V AC/DC
- Operating Temperature: -20°C to +60°C



Outline Dimensions

