



Fuse-link, LV, 160 A, AC 690 V, NH1, aM, IEC, dual indicator, live gripping lugs

Catalog No. 160NHM1B-690

EL-Nummer (Norway) 0001664151

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	160
Rated voltage			AC 690 V
Construction size			NH1
Utilization category			aM
Status indicator			dual (combination) indicator system
Description			live gripping lugs
Breaking Capacity		kA	120
Standard/Approval			IEC
Shape			square body with knife blade contacts
Standards/Regulations			IEC 60269-2 fuse system A DIN 43620 VDE 0636-2

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			NH1
Rated current		A	160
Rated voltage		V	690
Voltage type			AC
Rated switching capacity		kA	120
Utilization category			aM (switchgear protection)
Type of fuse status indicator			Combination fuse status indicator
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (PDF)	http://www1.cooperbusssmann.com/pdf/eb30bb45-9850-4820-a3b9-8e873de29a03.pdf
-------------------------	---