



Fuse-link, low voltage, 100 A, AC 415 V, 80 kA, BS88/A4, 27 x 110 mm, gM, BS, motor-rated



Powering Business Worldwide™

Part no. **100M125 415V AC BS88 FUSE**
 Catalog No. **CEO100M125**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	100
Motor current rating	I	A	100M125
Rated voltage			AC 415 V
Construction size			BS88/A4
Size			27 x 110 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder RS100H

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	100
Rated voltage		V	415
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No