



# Product data sheet

Power tools for trade & industry

Cordless Impact Driver/Wrench

## PRO GDS 18V-750 C



High-powered 1/2" cordless impact wrench combines performance with compactness

### The most important data

Battery voltage	18.0 V
Torque, max.	750 Nm
No-load speed	0-800 rpm

**Order number** 0 601 9L9 000

## Technical data

### Technical data

Torque adjustment range, min./max., 1st level	270 Nm
Torque adjustment range, min./max., 2nd level	380 Nm
Torque adjustment range, min./max., 3rd level	750 Nm
No-load speed	0-800 rpm
No-load speed (1st level)	0-800 rpm
No-load speed (2nd level)	0-1,500 rpm
No-load speed (3rd level)	0-2,400 rpm
Torque settings	3
Weight excl. battery	1.7 kg
Torque, max.	750 Nm
Impact rate	1,500-3,000 bpm
Impact rate (1st level)	0-1,500 bpm
Impact rate (2nd level)	0-2,300 bpm
Impact rate (3rd level)	0-3,000 bpm
Battery voltage	18.0 V
Tool holder	1/2" Square
Breakaway torque, max.	1,000 Nm
Packaging dimensions (width x length x height)	226 x 240 x 100 mm
BITURBO	No



# Product data sheet

Power tools for trade & industry

## Advantages:

- 750 Nm tightening torque and 1000 Nm breakaway torque combined with a head length of only 156 mm
- Ideal for metal workshops/locksmiths, industrial metal fabrication, vehicle maintenance, and general construction
- Innovative Secure Socket Release (activation via App) prevents the socket to get stuck on the bolt/nut

**HEAVY DUTY****PROFESSIONAL  
18V  
SYSTEM**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/au/en/wac/>

