



Main

Range of product	Harmony XAR
Accessory / separate part type	Battery charger
Accessory / separate part category	Electrical accessory

Complementary

[Us] rated supply voltage	100...240 V AC
Network frequency	50...60 Hz
Nominal output current	1.2 A at 5 V DC
Connections - terminals	5-position plug-in connector
Net weight	0.1 kg

Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...60 °C

Packing Units

Package 1 Weight	196 g
------------------	-------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.