

Product type designation

Product description

Distance piece MDS D124/D324/D424/RF320T

Support for mounting transponders with 27 mm diameter and 15 mm distance to metal

MOBY D/RF300 ISO/RF200 Spacer for MDS D124/D324/D424/D524 and RF320T Temperature range up to +180 °C Packing unit =

Minimum order quantity: 20 units



Suitability for use

Support is mounted with an M4 countersunk head screw, the transponder is snapped on

Mechanical data

Material

PPS

Color

black

Ambient conditions

Ambient temperature

- during operation
- during storage
- during transport

-25 ... +180 °C

-40 ... +180 °C

-40 ... +180 °C

Design, dimensions and weights

Height

22 mm

Diameter

36 mm

Further information / Internet-Links

Internet-Link

- to website: TIA Selection Tool
- to website: Selector SIMATIC NET SELECTION TOOL
- to the website: IWLAN
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

last modified:

<http://www.siemens.com/tia-selection-tool>
<https://support.industry.siemens.com/WW/view/en/67384964>
<http://www.siemens.com/iwlan>
<http://www.siemens.com/ident/rfid>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

03/23/2020