



Go To Step Search™ Screen

36917 -- *1 of 1 products*

Terminals and Splices

Ring and Spade Tongue Terminals

General **INFO**

Sales **INFO**

Customer Drawings
SPECIFICATIONS

Line Art

Line art represents typical product only.

<i>Searchable Features:</i>	
Terminal Shape	Ring Tongue
Body Style	SOLISTRAND
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Wire Range	1/0 [42.2-60.6 ²] AWG [mm]
Wire Range (CMA)	83,700-119,500
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	3/8 [9.53]
Stud Diameter	.375 [9.53] in. [mm]
Shape	RING-049
Heavy Duty	Standard
Packaging Method	Loose Piece
Material	Copper
Finish	Tin
<i>Other Properties:</i>	
Dim. C	.625 [15.88] Min. in. [mm]
Dim. E	1.529 [38.84] Max. in. [mm]
Dim. L	1.956 [49.69] Max. in. [mm]
Dim. W	.875 [22.23] in. [mm]
Barrel I.D. Min.	.444 [11.28] in. [mm]
Stock Thickness	.073 [1.85] Max. in. [mm]