IP67 SEALED CIRCULAR PLASTIC CONNECTOR

TE Connectivity (TE) IP67 Sealed Circular Plastic Connector is designed for power & signal wire-to-wire connection systems in a wide range of harsh environment applications. The connector is IP67/68 rated enabling it to withstand the harshest environments. It features a pre-positioned 1/4 turn coupling ring with positive lock and alignment features helping ease of installment. It's unique contact pattern for each position size helps prevent accidental mating with other position sizes.



Applications

- Outdoor LED lighting
- Architectural lighting

Electrical

Operating current: 7A (2P), 6A (3P & 4P)
 Operating voltage: 300 VAC Max
 Dielectric withstanding voltage: 1600 VAC

Mechanical

• Operating temperature: -25°C to +80°C

• 30 Cycles Durability

Product Specifications

Application specifications: 114-137041
 Product specifications: 108-137041

Materials

• Housing: 94V0 rated high

temperature resistant

thermoplastic

• Contact : Tin over nickel plated

copper alloy

Key Benefits


- Achieve a high level water proof solution with IP67 to IP68 rating
- Save space with a compact circular design
- Help prevent accidental mating with a unique contact pattern for each position sizes
- Help improve assembly through prepositioned 1/4 turn coupling ring with positive lock and alignment features
- Secure engagement through a clear locking sound when connection occurs




Product Selection Information

Part Number	Description
9-2834000-1	2P MALE CABLE ASSEMBLY
9-2834001-1	2P FEMALE CABLE ASSEMBLY
9-2834002-1	3P MALE CABLE ASSEMBLY
9-2834003-1	3P FEMALE CABLE ASSEMBLY
9-2834004-1	4P MALE CABLE ASSEMBLY-150MM
<u>9-2834005-1</u>	4P FEMALE CABLE ASSEMBLY-150MM

Dimensions





MATES WITH 2834001 SERIES.

te.com

© 2016 TE Connectivity Ltd. Family of Companies. All Rights Reserved. TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

1-1773883-9 JN 6/2016

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 The Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

