

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.


ALL RIGHTS RESERVED.

Tooling Drawing NO.

USB A: TR00662

USB B: TR00664

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		C	REVISE PER ECO-05-006320	01AUG05	TW	JH




- NOTES:
- 1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.
 - 2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.
 - 3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.
 - 4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 1700MM PER USB SPECIFICATIONS.
 - 5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

PART NO.	1487587-1	1487587-2	1487587-3
LENGTH(L)	1000	1300	830

AR	AR	AR	MR	COPPER FOIL, W: 5MM, 360° SOLDER	6
1	1	1	PC	Lable, 25x35mm, White 25x13mm	5
AR	AR	AR	KG	Overmold PVC, 40P, Color: White(WH01)	4
AR	AR	AR	MR	USB 2.0 Cable 28AWG*1P+26AWG*2C+Al/Mylar +Drain+Braid, Color: White(WH01).	3
1	1	1	EA	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 B Type.	2
1	1	1	EA	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 A Type.	1
-3	-2	-1	U/M	DESCRIPTION	ITEM

PIN ASSIGNMENT :



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

DWN BOVEY LIU 25FEB02

CHK J.HUNT 25FEB02

APVD J.HUNT 25FEB02

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
USB A TYPE TO USB B TYPE CABLE ASSEMBLY

SIZE CAGE CODE DRAWING NO RESTRICTED TO
A3 00779 C-1487587 -

CUSTOMER DRAWING SCALE N.T.S SHEET 1 OF 1 REV C