

ROLINE USB 3.2 Gen 2 Cable, PD, C-C, M/M, 4K UHD-1, 10Gbit/s, Emark, 100W, black, 0.5 m

Product No.	11.02.9056
Manufacturer	ROLINE
Manufacturer No.	11.02.9056
EAN (single piece)	7630049629141



Full-featured USB 3.1 / USB 3.2 Gen 2 cable with a data transmission rate of up to 10 Gbit/s and full Power Delivery support of up to 20V 5A!

- High quality USB 3.1 / USB 3.2 Gen 2 cable with improved shielding
- With the new reversible Type C connectors at both ends
- Gold-plated contacts for low wear at high plugging cycles
- Suitable for data transfer rates of up to 10 Gbit/s
- Supports USB Power Delivery to 20V / 5A
- Supports video transfer

Note: According to the current specifications of USB.org we have adapted the technical data of our USB 3 products. The new designation for the already known USB specifications has been changed to USB 3.2 Gen 1 (formerly USB 3.0 / USB 3.1 Gen 1) and USB 3.2 Gen 2 (formerly USB 3.1 / USB 3.1 Gen 2).

Technical specifications	
Manufacturer	ROLINE
Product group	Cable
Product type	USB 3.2 Cable
Colour	black
Length	0.5 m

Transfer quality	USB 3.2 Gen 2 SuperSpeed 10 Gbit/s (USB 3.1 Gen 2, USB 3.1)
Connection ports	USB Type C (USB-C) Male / USB Type C (USB-C) Male
Side 1 Connector Type	USB Type C (USB-C)
Side 1 Connector Gender	Male
Side 2 Connector Type	USB Type C (USB-C)
Side 2 Connector Gender	Male
Colour (Cable)	black
Max. resolution	3840 x 2160 @60Hz (4K, UHD-1)
Maximum data transfer rate	10 Gbit/s
Area of application	External
Supported charging technology	USB-PD - USB Power Delivery
Power (max.)	100 W
Cable shielding	Screened
Hand locking screws	no
Weight	27.3 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	100 mm
Package weight (single piece)	0.005 kg