



ENGLISH

Datasheet

RS Pro HSS M12 108 mm Counterbore Drill Bit, 20mm Cutter Diameter, 12 mm Screwed Shank

RS Stock No: **522-7480**



Product Details

RS Pro counterbore drill bit has HSS construction with M12 thread size. This 108 mm long drill bit has a cutter diameter of 20 mm and screwed shank diameter of 12 mm. The right hand cutting counterbore is designed to produce recessed holes for cap headed screws.

Features and Benefits

- 25.5 mm cutter length
- 13.5 mm pilot length
- Pilot diameter of 13 mm
- Threaded shank
- 108 mm overall length
- Made from HSS



Specifications:

Cutter Diameter	20 mm
Cutter Length	25.5 mm
Material	HSS
Overall Length	108 mm
Pilot Diameter	13 mm
Pilot Length	13.5 mm
Shank Diameter	12 mm
Shank Type	Screwed
Thread Size	M12
Number of Flutes	2