

ZC2JY33

limit switch lever ZC2JY - steel roller lever
variable length - -40..70°C



Price** : 84.00 USD

ZC2JY33 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE07 ZC2JE03 ZC2JE01 ZC2JE05 ZC2JE06 ZC2JE04 ZC2JE02
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal variable length)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature
Environmental characteristic	Standard environment Corrosive Low temperature

Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
GTIN	03389110635225
Package weight(Lbs)	0.13 lb(US) (0.059 kg)
Returnability	No

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------