

Product Information



1470POO075P30-11

EAN 4031582338515

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel centre made of Polypropylene, plain bearing

Technical Data	
Wheel diameter	75 mm
Width of Tread	25 mm
Centre hole	11 mm
Offset	25 mm
Swivel Interference	125 mm
Overall height	100 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.213 kg
Swivel Radius	62.5 mm
Hardness of tread	Shore D 65
Load capacity	40 kg
Load capacity (static)	80 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



1470POO075P30-11

EAN 4031582338515

