




All Polyester Vertical PCB Header: 2.54mm, Breakaway, MTA 100 (27)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought




TE Part #382575-2
2MM MINI-SHUNT ASSEMBLY 15 AU




TE Part #1-480673-0
09P .140 MNL CAP PM NAT




TE Part #350766-4
03P UMNL PLUG HSG UL94V0



TE Part #280371-2
4P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #280372-2
6P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #5749081-1
100 50SR BSHLL KIT,M J-SCR




TE Part #1761685-7
IDC LOW PRO HDR 20P VERT SHT LAT



TE Part #794059-1
MINI UMNL PIN L/P



TE Part #1-1734328-1
Mini USB AB R/A,Rcpt,SMT,TRAY, 0.6 mm



TE Part #280378-2
4P MODU II SHRD HDR, RT ANG, 0.38 AU

Documents

Product Drawings

20P MTA100 HDR ASSY,NARROW AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-644884-0_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-644884-0_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-644884-0_C.3d_stp.zip

English

Customer View Model



[ENG_CVM_2-644884-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_2-644884-0_A.2d_dxf.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_2-644884-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English