




Datasheet

Product Name:	MIL-W-22759/11 24AWG
Product Discription:	MIL-W-22759/11 24AWG
Specification No.:	
Customer's Name:	

Description					Construction					
Rated Voltage:	600V				Conductor	Stranded Sliver plated copper				
Rated Temperature:	200°C				Size(AWG)	24				
Reference Standard:	MIL-W-22759/11				Construction(±0.008mm)	19/0.127				
Cross Section					Stranded Dia.(mm)Ref.	0.63				
					Insulation Material	PTFE				
					Insulation Color	ANY COLOR				
					Ave Thickness(mm)	0.25				
					Insulation Dia.(±0.08mm)	1.12				
Marking					Remark:					
No marking on the cable jacket					8776219 Red 8776216 Blue 8776203 Black 8776213 White 8776207 Brown					
Applications					Characteristics					Customer Approve
These wires are ideal for internal wiring of appliances, electronic equipment and other applications.					Test Item	Standard Value				Seal & Stamp Signature: Date:
					Test Material	PTFE(ROHS)				
					Insulation resistance(20°C MΩ*m)	1000				
					Vol. Tesr(AC.V.60S) (V)	2000				
					Flammability Test	VW-1				
					Max.DC Resistance(20°C Ω/km)	77.4(MAX)				
Revisions										
Version	Description	Drawn by	Approved by	Date						
0	New document issue	Danniel	Jason	19/05/2015						