



INSULATED SPANNER 10MM

- Open off set at 15° for easier use
- Approved for live working up to 1,000 volts
- Nonslip handle for maximum comfort
- Chrome vanadium steel construction
- Designed and manufactured to DIN3114 IEC60900 standards

Insulated Open Ended Spanner 10mm

General information

Country of origin: Taiwan
Barcode: 5020385044814
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002176
UNSPSC: 27111706

Dimensions

Net weight (g): 37
Length: 114 mm

Attributes

Product type: Insulated Spanners
Material: CrV
Certificates: VDE
Size: 10 mm
Tethering facility: No
Insulated: Yes
Spanner type: Regular
Unit of measurement: Metric
Jaw diameter: 25.0
Jaw height (mm): 8.1
Offset angle jaw (°): 15

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden