


Cover 3NP1123 (NH000 up to 160 A), H: 250 mm W: 600 mm



| Model                                            |               |
|--------------------------------------------------|---------------|
| product brand name                               | SIVACON S4    |
| design of the surface                            | powder-coated |
| net weight                                       | 1.28 kg       |
| height                                           | 250 mm        |
| width                                            | 600 mm        |
| depth                                            | 10 mm         |
| installation width for cabinet installation      | 600 mm        |
| mounting height for device equipment can be used | 250 mm        |
| material                                         | sheet-steel   |
| reference code according to IEC 81346-2          | UC            |

| Approvals Certificates   |       |
|--------------------------|-------|
| General Product Approval | other |

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)

Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/lowvoltage/catalogs>  
Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2025-6BA18>  
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2025-6BA18>  
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)  
[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ2025-6BA18](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2025-6BA18)  
CAx-Online-Generator  
<http://www.siemens.com/cax>  
Tender specifications  
<http://www.siemens.com/specifications>



