

M4/6.4A.P



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

General Information

Extended Product Type:	M4/6.4A.P
Product ID:	1SNA195638R2300
EAN:	3472591956382
Catalog Description:	M4/6.4A.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
Long Description:	- Reliable electrical and mechanical contact with the rail, - Flexibility: snap onto symmetrical and asymmetrical rails.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Green-Yellow
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ² Screw Clamp / With Insulated Ferrule 1x 2.5 mm ²
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225017U1000
EAC Certificate:	1SND161009A1100
EAN:	3472591956382
ETIM 4:	EC000901 - Ground terminal block
ETIM 5:	EC000901 - Ground terminal block
ETIM 6:	EC000901 - Ground terminal block
Environmental Information:	1SND220004E1002
Flammability According to UL94:	V0
Function:	Ground
Gauge Type:	A4
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Insulation Material:	Polyamide
Invoice Description:	M4/6.4A.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	4
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472591956382
Package Level 1 Gross Weight:	1.1 kg
Package Level 1 Height:	64 mm

Package Level 1 Length:	155 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	126 mm
Package Level 2 Gross Weight:	11.350 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	500 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	24000 piece
Pollution Degree:	3
Product Main Type:	M4/6.4A.P
Product Name:	Terminal block
Product Net Depth:	40.5 mm
Product Net Height:	63.5 mm
Product Net Weight:	22 g
Product Net Width:	6 mm
Product Packing Type:	Box
RMRS Certificate:	1SND161007A1101
Rated Cross-Section:	4 mm ²
Rated Short-time Withstand Current (I _{cw}):	for 1 s 480 A
Recommended Screw Driver:	4 mm
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	green/yellow Screw Clamp Terminal Blocks M4/6.4A.P
Spacing:	6 mm
Sub-Function:	4 connections
Sub-Function 2:	Screw rail connection
Sub-Function 3:	4 connections
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
Wire Stripping Length:	9.5 mm
Number of Potentials:	1

