

M18 BLHPTXL-502C

M18™ FORCE LOGIC™ BRUSHLESS XL PRESS TOOL

- New compact brushless motor in FORCE LOGIC™ press tools delivers up to 10% faster connections and 20% more run time
- FORCE LOGIC™ press indicator: provides visual confirmation of a quality connection
- Extended press range up to 108 mm in copper, C- steel & stainless steel & up to 4" in steel pipe
- One hand operated tool for over head applications and working in narrow spaces
- Adjustable stroke length allows usage of all standard MILWAUKEE® J18 jaws + most common competitive jaws available on the market
- FORCE LOGIC™ long life reliability: No press cycle limitation within the 3 year maintenance interval
- Auto-cycle ensures a full press cycle is completed with every press connection
- Battery-tool communication: press operation doesn't start to prevent incomplete pressing in case of low charged battery. Pre-press battery check ensures enough charge to complete each press
- On board fuel gauge and LED light
- Brushless motor, REDLITHIUM™ battery pack and REDLINK™ electronic deliver power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

Max. press size in c-steel & stainless steel (mm)	108
Max. press size in composite (mm)	110
Max. press size in copper (mm)	108
Max. press size in steel (Inch)	102
Weight with battery pack (EPTA) (kg)	3.9 (M18 B5)
Kit included	2 x M18 B5 Battery packs, M12-18 C Charger, PACKOUT™ box
Article Number	4933479441

