

# ETU17N

## 24 Hour/7 Day Slimline Digital Plug-in Time Controller

### Features & Benefits

- Top side display for ease of viewing when in use
- Slimline plug-in control
- 7 Day programming
- 7 ON/OFF programmes over a choice of day groups or individual days
- Manual Override (Self-cancelling)
- Optional random switching feature
- Rechargeable battery backup



### Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Plug-in
Earth Class Rating	Class II
Operating Temperature	-10°C to +35°C
Setting Type	Digital
Battery Type	NiMH 3.6V 40mAh Rechargeable Battery (Non Replaceable)
Power Reserve	1000 Hours
Program Modes	24 Hour/7 Day, Random

# Data sheet

## ETU17N

Time / Immersion & General Purpose Timeswitches

Socket Outlet	Single Gang UK Plug
Switch type	Single Pole
Standby Consumption	<0.2W
Switch rating	13A Resistive, 2500W Incandescent/Halogen, 500W Fluorescent, 100W LED
Shortest Switching Time	1 Minute
Programmable Slots	7 ON, 7OFF
Permanent ON Facility	Yes (Until next programme change)

### General

Weight (g)	113
Height (mm)	81
Width (mm)	60
Depth (mm)	65
Body Construction	Polycarbonate
Product Colour	White
EAN Number	5012483015292
Guarantee Period	3 Years

# Data sheet

## ETU17N

Time / Immersion & General Purpose Timeswitches

### Line Diagrams

