



Mosaic™ Franco-Belgian socket outlets

Cat. No.(s): 0 771 10/11/12/13/14/15/16/17/18/19
 0 771 26/40/41/45/46/47/48/49/99
 0 787 01 - 0 791 21 - 0 792 14/71



0 771 11



0 771 19

1. USE

2 P+E and 2 P socket outlets Franco-Belgian standard.
 The mechanism can be flush-mounted or surface-mounted.
 To be equipped with plates.

Antimicrobial* sockets:

These products are made of silver-ion based antimicrobial* material.
 This technology eliminates bacteria, fungi and viruses without creating any immunisation or resistance effects (physical, rather than chemical, destruction).


Particularly suitable for healthcare establishments (hospitals, clinics, nursing homes, laboratories, waiting rooms, etc.) and more generally for areas subject to hygiene restrictions (industrial, shared and restaurant kitchens, waste, etc.).

These products offer an additional way of ensuring the non-proliferation of bacteria, fungi and viruses without interfering with cleaning protocols.

2. RANGE

Cat. No.	Designation	Finishes
0 771 10	2 P socket	White
0 771 11/40/99	2 P+E socket	White
0 791 21	2 P+E socket	Anthracite
0 792 14/71	2 P+E socket	Aluminum
0 787 01	2 P+E socket	White antimicrobial*
0 771 16/46	2 P+E socket	Green antimicrobial*
0 771 17/47	2 P+E socket	Orange antimicrobial*
0 771 18/41	2 P+E socket	Red antimicrobial*
0 771 19/49	Flush-cover 2 P+E	White
0 771 45	45° angled 2 P+E socket	White
0 771 48	45° angled 2 P+E socket with indicator light	White antimicrobial*
0 771 12	2 P+E Socket with indicator light	White antimicrobial*
0 771 13	2 P+E Socket special trapping	White
0 771 14	Tamperproof 2 P+E Socket	Red
0 771 15	Tamperproof 2 P+E Socket with indicator light	Red antimicrobial*
0 771 26	2 P+E socket with indicator light	Red antimicrobial*

3. OVERALL DIMENSIONS (mm)



References	A	B	C	D
0 771 10/11/12/16/17/18/19/26 0 771 40/41/46/47/49/99 0 787 01 - 0 791 21 - 0 792 14/71	45	45	38.5	8.5
0 771 45/48	45	45	39	8.5
0 771 13	45	45	36.5	8.5
0 771 14/15	45	45	37	9

4. CONNECTION

Automatic terminals:

Cat. Nos: 0 771 10/11/12/16/17/18/19/26/40/41/45/46/47/48/49/99
 0 787 01 - 0 791 21 - 0 792 14/71


Terminal capacity up to: 2 x 2.5 mm²

Stripping: 12 mm


Screw terminals:

Cat. No.	Capacity	Stripping	Screwdriver
0 771 13	2 x 4 mm ²	9 mm	4 mm Flat-blade
0 771 14/15	2 x 2.5 mm ²	9 mm	


4. CONNECTION




0 771 10/11/12/16/17/18/19/26/32/33
 0 771 40/41/46/47/49/99
 0 787 01/04 - 0 791 21 - 0 792 14/71



0 771 45/48



0 771 13



0 771 14/15

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

- Impact tests: IK 04 (mounted product)
 IK 07 for Cat. No 0 771 19/45/48 (mounted product)
- Protection against solid bodies and liquids: IP 41

■ 5.2 Material characteristics

- Halogen free
- UV resistant
- Self-extinguishing:
 + 850°C / 30 s for insulating parts holding live parts in place.
 + 650°C / 30 s for other parts made of insulating materials.
- Bases: PC
- Covers: - PC White RAL 9003
 - PC Red RAL 3020
 - PC Green RAL 6016
 - PC Orange RAL 2003
 - PC Anthracite
 - PC painted Aluminium
- Covers for references antimicrobial*: PC + antimicrobial treatment*.

■ 5.3 Electrical characteristics

Voltage: 250 V~
 Current: 16 A

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C
 Operating temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.
 Do not use: acetone, tar remover, trichloroethylene.

■ 6.1 Resistance to the cleaning agents:

Hexane (NF C 61-314), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning substances, Pre-impregnated wipes.

■ 6.2 Resistance to type cleaning hospital:

Anios, Surfanios, Bactylisine, hydrogen peroxide (35%).

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. ACCESSORIES

Indicator light for:

Socket outlets	LED indicator with 2 wires to cable
0 771 12 0 771 15 0 771 26 0 771 48	0 676 64 (230 V - 2.4 mA)

Tamperproof for:

Socket outlet	Tamperproof insert
0 771 14 0 771 15	0 502 99

8. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
 See e. catalogue.

* Contains a silver compound to antagonize the growth of bacteria on the surface.