

## ReXel Momentum X410 Cross Cut Paper Shredder

The power to shred more! The Momentum X410 paper shredder shreds up to 10 sheets (80 gsm) in to P-4 (4x28mm) cross cut pieces, with a 23L bin which holds 225 A4 sheets.



## Attributes

- Shreds up to 10 sheets in one pass (80gsm)
- P-4 (4x28mm), 1 x A4 sheet into 400 cross cut pieces
- 23L bin capacity, 225 A4 sheets
- Anti jam technology, shredder automatically stops and reverses when too much paper is inserted
- Easily shreds multiple documents, even with staples and paperclips on the corners
- Touch panel operation for easy use
- 2 Year Warranty
- 2 Year Cutter Warranty



## Specifications

Number	2104571
Colour	black
Dimensions (W x H x D)	356 x 423 x 238 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	220
Run Time From Cold (min)	6
Run Time/Cool Down Time (min)	6/60
Shredded Particle Width mm	4x28
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	11
Cutting Capacity sheets (80gsm paper)	10
Container/collection volume in l	23
Shreds	Paper, Paper clips & Staples
Power consumption (W)	280
Noise Level (dBA)	62
Period of Warranty (Years)	2
Location	Office
Number Of Users	1-2
Weight	6500 g
Pallet quantity	36
EAN code	5028252523127