



Notes

- 1. TNC Female Bulkhead Straight
 - 2. SMA Male Right Angle
 - 3. Heatshrink
 - 4 Overall length 200mm
- Attenuation (Max) : -1.5dB
 VSWR (Max) : 1.5
 Nominal Impedance: 50ohm
 RoHS compliant

NOT TO SCALE

All Dimensions in mm



DESCRIPTION				
Cable Assy TNC(F) Bulkhead to SMA(M)R/A cable Assy 200mm				
FILENAME	DRAWN BY	DATE	REVISED	PAGE
CBA-TNCF-SMAMR-1.VSD	John Fairall		13/01/2012	1 of 1
REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
N/A	1	First Issue	1.8.09	
	2			
	3			
	4			
	5			
	6			