


G9 LED ALL-GLASS

SLD8702X2S

2,2 W - 250lm - 3000K



DIMENSIONS	A	B	C
1	53	15	

GENERAL INFORMATIONS	
Code	SLD8702X2S
Ean	8031453025342
Family	G9 LED ALL-GLASS
Product line	G9
Technology	LED
Operating temperature (° C)	-20 - +40
Years warranty	2
LIGHTING DATA	
CCT (K)	3000
Luminous flux (lm)	250
Beam (°)	330
Luminous Efficacy (lm/W)	115
Color rendering (CRI)	>80
Standard Deviation Colour Matching - SDCM	6
Chromatic Coordinates y	0,4033
Chromatic Coordinates x	0,4339
Stroboscopic Visibility Measure - SVM	0,9

TECHNICAL FEATURES	
Base	G9
Power (W)	2,2
Energy Consumption ON mode (kWh/1000h)	3
Supply voltage (V) / Max (V)	220 / 240
Power frequency (Hz)	50/60
Current consumption (mA)	22
Dimmer compatibility	NO
On/off cycles	20000
Nominal life (h)	20000
Directional / Non-directional	NDLS
Mains voltage YES / NO	MLS
Factor Total Mains - FTM	1
Survival factor (2019/2015)	0,9
Lumen Maintenance factor (2019/2015)	0,948
PACKAGING	
Packaging	BOX
Pack	10 / 50
Gross weight (Kg)	2
Net weight (Kg)	0.018