Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Set of cable gland + nut M25 for EMC application, IP68, UL approved



NSYCGHF25

EAN Code: 3606481360120

Main

_		
Range	PanelSeT	
Product or component type	Cable gland	
Accessory / separate part category	Cable management accessory	
Range compatibility	PanelSeT PanelSeT CRN PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X	
Mounting location	Enclosure top Enclosure bottom	
Cable entry	Cable gland M25	
Device composition	1 cable gland 1 lock nut 1 seal	
Quantity per set	Set of 5	
Material	Body: nickel plated brass Seal: CR (chloroprene)	

Complementary

Colour	Grey
Surface finish	Chromium plated
Fixing mode	Screwed By nut
Height	38.7 mm
Net weight	0.05 kg

Environment

Product certifications	UL
Environmental characteristic	EMC directive
Flame retardance	V2 conforming to UL 94
Ambient air temperature for operation	-20100 °C permanent -40150 °C intermittent
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm

Package 1 Width	14.500 cm
Package 1 Length	15.000 cm
Package 1 Weight	50.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	11.000 cm
Package 2 Width	28.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.366 kg

Logistical informations

Country of origin TR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Take-back

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
Use Again		
○ Repack and remanufacture		

No