

1837C

Rechargeable LED spotlight for building yards

CE IP65

Features

- 3 brightness settings
- Battery charger: input: 100-240V AC - 50/60Hz; output: 15V 1.5A
- Charging time: 4 hours
- 3-LED charge indicator
- Can rotate up to 180°
- Class of protection IP65
- Impact resistance IK07

	art.		LxHxI mm	Lm	h	g
018370210	1837C/2100		220x225x70	2100	2.5	1108
018370430	1837C/4300		266x236.6x59	4300	1.5	1318
018370970		Power supply for LED spotlights 1837C/2100-4300				

