

Roof plate with cable entry IP40, W: 850 mm D: 800 mm



Model	
product brand name	SIVACON S4
product designation	top plate
design of the product	cable entry
design of the surface	zinc plated
design of the product EMC version	No
Protection class	
protection class IP	IP40
Suitability	
suitability for use for outside use	No
Appearance	
color	miscellaneous
Product details	
product component	
• cable entry	Yes
• ventilation	No
Mechanical Design	
height	25.5 mm
width	850 mm
depth	800 mm
net weight	13 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



EG-Konf.



VDE

[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2300-8BA08>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2300-8BA08>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2300-8BA08

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/30/2025 

